

1. Facade



Caution:
 Using the heating function, the liquid should be kept the minimum above the water line. Otherwise cause the sink doubt be damaged.

2. Specifications

Ultrasonic Benchtop Cleaner Specifications		
Item	WB-300	WB-650
External dimensions (mm)	327*265*315	530*327*400
Tank Size (mm)	300*235*150	500*297*200
Cleaning basket size (mm)	250*195*100	450*240*150
Maximum capacity (L)	12.6	33
Operation capacity(L)	9.2	25.5
Numbers of Oscillators	6	11
Frequency(KHz)	28 or 40 KHz	28 or 40 KHz
Maximum output power (W)	300W	650W
Heating power (W)	500	800
Max. Power consumption (including heating) (A)	4.5A(AC110V) 2.7A(AC220V)	5.4A(AC220V)
Shell Material	Stainless steel lines	
Power supply	AC110 or AC220V 50/60Hz	OnlyAC220V 50/60Hz
Temperature control	Automatic control of heating systems, heating maximum temperature 75 °C	
Cleaning Time Control	Electronic set the timer function (from 0 to 99 minutes)	

WHIRL BEST INTERNATIONAL Co., LTD.

TEL:+886-3-496-2308~9 FAX:+886-3-464-3587 <http://www.WHBEST.com.tw>

e-mail:whbest.a168@msa.hinet.net No.15, Yongping Rd., Yangmei City, Taoyuan County 326, Taiwan (R.O.C.)

3. Advanced LCD panel control system




- ✧ Display and set quickly and easily for use.
- ✧ Conversational illustration, simple operation
- ✧ Parameter Display:clear whether setting parameters or the actual parameters - bright LCD panel display
- ✧ Easy cleaning time memory storage mode operation, such as "plug it in, set up, cleaning, storage "
- ✧ Heater 20-75 ° C, the temperature is adjustable, LCD display temperature setpoint and actual temperature
- ✧ Automatically saved cleaning set, display the last saved parameters at boot
- ✧ Countdown timer to take continuous work
- ✧ Degassing function :preset pulse mode actuator for degassing operation of the function icon LCD panel
- ✧ With ultrasonic drive pulse wave during heating, to avoid delay cavity effect
- ✧ Electronic digital timer, automatic shutdown after cleaning time arrives
- ✧ Zero function, at any time to restore parameters to factory setting
- ✧ P33 protection rating: through cable and waterproof sealing frame, so that the best protection class piece welded drain valve using high-performance stainless steel valves
- ✧ Using high-efficiency industrial grade temperature type ultrasonic oscillator and special adhesive glue, to long life features
- ✧ The heating system uses industrial-grade silicone soft board power heating film, heating speed and long life

4. Advanced surface treatment of stainless steel exterior

Material

Excellent imported checked SUS

Slap-up and robust checked SUS,
attractive and durable.



- ◇ European and American art of the grain surface using surface treatment technology, comparable to European and American products, elegant

5. Bilateral handle high load

Handle

Aluminum Alloy Handle

Industrial level, longer lifespan and high strength
which can bear heavy duty workpieces



WHIRL BEST INTERNATIONAL Co., LTD.

TEL:+886-3-496-2308~9 FAX:+886-3-464-3587 <http://www.WHBEST.com.tw>

e-mail:whbest.a168@msa.hinet.net No.15, Yongping Rd., Yangmei City, Taoyuan County 326, Taiwan (R.O.C.)

6. Clean stainless steel inner tank completely



Tank

SUS Tank

Made in imported SUS 304 with special surface treatment to expand the service time and resistance to corrosion from ultrasonic cavitation

7. Professional-grade ball-type drain valve


Valve

Ball Valve

One-piece welding process 1/2" valve, excellent waterproof and durability



9. Industrial-grade material selection



Features: transducer arrangement
 Parameter consistency
 Best output design
 Imported special adhesive glue and advanced bonding process



All stainless steel high strength pressure line end
 Son, has a very high tensile Strength, shear strength and shock Performance. Corrosion resistance, high Temperature. Can significantly enhance the operating speed Degree, avoid high volatility at or Oscillator off or off-line



Advanced intelligent microprocessor design, with pulse, temperature, time, self-protection and other functions, signal output steady, significant cleaning effect




10. Standard accessories

WHIRL BEST INTERNATIONAL Co., LTD.
 TEL:+886-3-496-2308~9 FAX:+886-3-464-3587 <http://www.WHBEST.com.tw>
 e-mail:whbest.a168@msa.hinet.net No.15, Yongping Rd., Yangmei City, Taoyuan County 326, Taiwan (R.O.C.)

- 1). Stainless steel wash basket:
(1). 300W USE(250*195*100mm)




- (2). 650W USE (450*240*150mm)



2). Stainless steel dust lid

WHIRL BEST INTERNATIONAL Co., LTD.
TEL:+886-3-496-2308~9 FAX:+886-3-464-3587 <http://www.WHBEST.com.tw>
e-mail:whbest.a168@msa.hinet.net No.15, Yongping Rd., Yangmei City, Taoyuan
County 326, Taiwan (R.O.C.)



11. Professional protective packaging to prevent the transport collision

